




























































PART NUMBERS

Tubing | PEEK

WVR catalog number	Part description and detail	Color
5' PEEK tubing		
SGEA1302002500-5F	1/16" OD x 0.0025" ID x 5' length PEEK tubing, natural	Natural ●
SGEA1302004006-5F	1/16" OD x 0.004" ID x 5' length PEEK tubing, black	Black ●
SGEA1302005001-5F	1/16" OD x 0.005" ID x 5' length PEEK tubing, red	Red ●
SGEA1302007002-5F	1/16" OD x 0.007" ID x 5' length PEEK tubing, yellow	Yellow ●
SGEA1302010003-5F	1/16" OD x 0.010" ID x 5' length PEEK tubing, blue	Blue ●
SGEA1302013004-5F	1/16" OD x 0.013" ID x 5' length PEEK tubing, orange	Orange ●
SGEA1302015000-5F	1/16" OD x 0.015" ID x 5' length PEEK tubing, natural	Natural ●
SGEA1302015008-5F	1/16" OD x 0.015" ID x 5' length PEEK tubing, gray	Gray ●
SGEA1302020004-5F	1/16" OD x 0.020" ID x 5' length PEEK tubing, orange	Orange ●
SGEA1302030005-5F	1/16" OD x 0.030" ID x 5' length PEEK tubing, green	Green ●
SGEA1302030001-5F	1/16" OD x 0.030" ID x 5' length PEEK tubing, red	Red ●
SGEA1302040000-5F	1/16" OD x 0.040" ID x 5' length PEEK tubing, natural	Natural ●
SGEA1301002500-5F	1/32" OD x 0.0025" ID x 5' length PEEK tubing, natural	Natural ●
SGEA1301004006-5F	1/32" OD x 0.004" ID x 5' length PEEK tubing, black	Black ●
SGEA1301005001-5F	1/32" OD x 0.005" ID x 5' length PEEK tubing, red	Red ●
SGEA1301007002-5F	1/32" OD x 0.007" ID x 5' length PEEK tubing, yellow	Yellow ●
SGEA1301010003-5F	1/32" OD x 0.010" ID x 5' length PEEK tubing, blue	Blue ●
SGEA1301015000-5F	1/32" OD x 0.015" ID x 5' length PEEK tubing, natural	Natural ●
SGEA1301015008-5F	1/32" OD x 0.015" ID x 5' length PEEK tubing, gray	Gray ●
SGEA1301020004-5F	1/32" OD x 0.020" ID x 5' length PEEK tubing, orange	Orange ●
SGEA1304002000-5F	360 μm OD x 50 μm (0.002") ID x 5' length PEEK tubing, natural	Natural ●
SGEA1304003006-5F	360 μm OD x 75 μm (0.003") ID x 5' length PEEK tubing, black	Black ●
SGEA1304004001-5F	360 μm OD x 100 μm (0.004") ID x 5' length PEEK tubing, red	Red ●
SGEA1304005005-5F	360 μm OD x 125 μm (0.005") ID x 5' length PEEK tubing, green	Green ●
SGEA1304006002-5F	360 μm OD x 150 μm (0.006") ID x 5' length PEEK tubing, yellow	Yellow ●
SGEA1303062000-5F	1/8" OD x 0.062" ID x 5' length PEEK tubing, natural	Natural ●
SGEA1303080000-5F	1/8" OD x 0.080" ID x 5' length PEEK tubing, natural	Natural ●
10' PEEK tubing		
SGEA1302002500-10F	1/16" OD x 0.0025" ID x 10' length PEEK tubing, natural	Natural ●
SGEA1302004006-10F	1/16" OD x 0.004" ID x 10' length PEEK tubing, black	Black ●
SGEA1302005001-10F	1/16" OD x 0.005" ID x 10' length PEEK tubing, red	Red ●
SGEA1302007002-10F	1/16" OD x 0.007" ID x 10' length PEEK tubing, yellow	Yellow ●
SGEA1302010003-10F	1/16" OD x 0.010" ID x 10' length PEEK tubing, blue	Blue ●
SGEA1302013004-10F	1/16" OD x 0.013" ID x 10' length PEEK tubing, orange	Orange ●
SGEA1302015000-10F	1/16" OD x 0.015" ID x 10' length PEEK tubing, natural	Natural ●
SGEA1302015008-10F	1/16" OD x 0.015" ID x 10' length PEEK tubing, gray	Gray ●
SGEA1302020004-10F	1/16" OD x 0.020" ID x 10' length PEEK tubing, orange	Orange ●
SGEA1302030005-10F	1/16" OD x 0.030" ID x 10' length PEEK tubing, green	Green ●
SGEA1302030001-10F	1/16" OD x 0.030" ID x 10' length PEEK tubing, red	Red ●
SGEA1302040000-10F	1/16" OD x 0.040" ID x 10' length PEEK tubing, natural	Natural ●
SGEA1301002500-10F	1/32" OD x 0.0025" ID x 10' length PEEK tubing, natural	Natural ●
SGEA1301004006-10F	1/32" OD x 0.004" ID x 10' length PEEK tubing, black	Black ●
SGEA1301005001-10F	1/32" OD x 0.005" ID x 10' length PEEK tubing, red	Red ●
SGEA1301007002-10F	1/32" OD x 0.007" ID x 10' length PEEK tubing, yellow	Yellow ●
SGEA1301010003-10F	1/32" OD x 0.010" ID x 10' length PEEK tubing, blue	Blue ●
SGEA1301015000-10F	1/32" OD x 0.015" ID x 10' length PEEK tubing, natural	Natural ●
SGEA1301015008-10F	1/32" OD x 0.015" ID x 10' length PEEK tubing, gray	Gray ●
SGEA1301020004-10F	1/32" OD x 0.020" ID x 10' length PEEK tubing, orange	Orange ●

Tubing | PEEK continued

VWR catalog number	Part description and detail	Color
SGEA1304002000-10F	360 µm OD x 50 µm (0.002") ID x 10' length PEEK tubing, natural	Natural 
SGEA1304003006-10F	360 µm OD x 75 µm (0.003") ID x 10' length PEEK tubing, black	Black 
SGEA1304004001-10F	360 µm OD x 100 µm (0.004") ID x 10' length PEEK tubing, red	Red 
SGEA1304005005-10F	360 µm OD x 125 µm (0.005") ID x 10' length PEEK tubing, green	Green 
SGEA1304006002-10F	360 µm OD x 150 µm (0.006") ID x 10' length PEEK tubing, yellow	Yellow 
SGEA1303062000-10F	1/8" OD x 0.062" ID x 10' length PEEK tubing, natural	Natural 
SGEA1303080000-10F	1/8" OD x 0.080" ID x 10' length PEEK tubing, natural	Natural 
50' PEEK tubing		
SGEA1302002500-50F	1/16" OD x 0.0025" ID x 50' length PEEK tubing, natural	Natural 
SGEA1302004006-50F	1/16" OD x 0.004" ID x 50' length PEEK tubing, black	Black 
SGEA1302005001-50F	1/16" OD x 0.005" ID x 50' length PEEK tubing, red	Red 
SGEA1302007002-50F	1/16" OD x 0.007" ID x 50' length PEEK tubing, yellow	Yellow 
SGEA1302010003-50F	1/16" OD x 0.010" ID x 50' length PEEK tubing, blue	Blue 
SGEA1302013004-50F	1/16" OD x 0.013" ID x 50' length PEEK tubing, orange	Orange 
SGEA1302015000-50F	1/16" OD x 0.015" ID x 50' length PEEK tubing, natural	Natural 
SGEA1302015008-50F	1/16" OD x 0.015" ID x 50' length PEEK tubing, gray	Gray 
SGEA1302020004-50F	1/16" OD x 0.020" ID x 50' length PEEK tubing, orange	Orange 
SGEA1302030005-50F	1/16" OD x 0.030" ID x 50' length PEEK tubing, green	Green 
SGEA1302030001-50F	1/16" OD x 0.030" ID x 50' length PEEK tubing, red	Red 
SGEA1302040000-50F	1/16" OD x 0.040" ID x 50' length PEEK tubing, natural	Natural 
SGEA1301002500-50F	1/32" OD x 0.0025" ID x 50' length PEEK tubing, natural	Natural 
SGEA1301004006-50F	1/32" OD x 0.004" ID x 50' length PEEK tubing, black	Black 
SGEA1301005001-50F	1/32" OD x 0.005" ID x 50' length PEEK tubing, red	Red 
SGEA1301007002-50F	1/32" OD x 0.007" ID x 50' length PEEK tubing, yellow	Yellow 
SGEA1301010003-50F	1/32" OD x 0.010" ID x 50' length PEEK tubing, blue	Blue 
SGEA1301015000-50F	1/32" OD x 0.015" ID x 50' length PEEK tubing, natural	Natural 
SGEA1301015008-50F	1/32" OD x 0.015" ID x 50' length PEEK tubing, gray	Gray 
SGEA1301020004-50F	1/32" OD x 0.020" ID x 50' length PEEK tubing, orange	Orange 
SGEA1304002000-50F	360 µm OD x 50 µm (0.002") ID x 50' length PEEK tubing, natural	Natural 
SGEA1304003006-50F	360 µm OD x 75 µm (0.003") ID x 50' length PEEK tubing, black	Black 
SGEA1304004001-50F	360 µm OD x 100 µm (0.004") ID x 50' length PEEK tubing, red	Red 
SGEA1304005005-50F	360 µm OD x 125 µm (0.005") ID x 50' length PEEK tubing, green	Green 
SGEA1304006002-50F	360 µm OD x 150 µm (0.006") ID x 50' length PEEK tubing, yellow	Yellow 
SGEA1303062000-50F	1/8" OD x 0.062" ID x 50' length PEEK tubing, natural	Natural 
SGEA1303080000-50F	1/8" OD x 0.080" ID x 50' length PEEK tubing, natural	Natural 
100' PEEK tubing		
SGEA1302002500-100F	1/16" OD x 0.0025" ID x 100' length PEEK tubing, natural	Natural 
SGEA1302004006-100F	1/16" OD x 0.004" ID x 100' length PEEK tubing, black	Black 
SGEA1302005001-100F	1/16" OD x 0.005" ID x 100' length PEEK tubing, red	Red 
SGEA1302007002-100F	1/16" OD x 0.007" ID x 100' length PEEK tubing, yellow	Yellow 
SGEA1302010003-100F	1/16" OD x 0.010" ID x 100' length PEEK tubing, blue	Blue 
SGEA1302013004-100F	1/16" OD x 0.013" ID x 100' length PEEK tubing, orange	Orange 
SGEA1302015000-100F	1/16" OD x 0.015" ID x 100' length PEEK tubing, natural	Natural 
SGEA1302015008-100F	1/16" OD x 0.015" ID x 100' length PEEK tubing, gray	Gray 
SGEA1302020004-100F	1/16" OD x 0.020" ID x 100' length PEEK tubing, orange	Orange 
SGEA1302030005-100F	1/16" OD x 0.030" ID x 100' length PEEK tubing, green	Green 
SGEA1302030001-100F	1/16" OD x 0.030" ID x 100' length PEEK tubing, red	Red 
SGEA1302040000-100F	1/16" OD x 0.040" ID x 100' length PEEK tubing, natural	Natural 
SGEA1301002500-100F	1/32" OD x 0.0025" ID x 100' length PEEK tubing, natural	Natural 
SGEA1301004006-100F	1/32" OD x 0.004" ID x 100' length PEEK tubing, black	Black 
SGEA1301005001-100F	1/32" OD x 0.005" ID x 100' length PEEK tubing, red	Red 
SGEA1301007002-100F	1/32" OD x 0.007" ID x 100' length PEEK tubing, yellow	Yellow 
SGEA1301010003-100F	1/32" OD x 0.010" ID x 100' length PEEK tubing, blue	Blue 
SGEA1301015000-100F	1/32" OD x 0.015" ID x 100' length PEEK tubing, natural	Natural 
SGEA1301015008-100F	1/32" OD x 0.015" ID x 100' length PEEK tubing, gray	Gray 
SGEA1301020004-100F	1/32" OD x 0.020" ID x 100' length PEEK tubing, orange	Orange 
SGEA1304002000-100F	360 µm OD x 50 µm (0.002") ID x 100' length PEEK tubing, natural	Natural 
SGEA1304003006-100F	360 µm OD x 75 µm (0.003") ID x 100' length PEEK tubing, black	Black 
SGEA1304004001-100F	360 µm OD x 100 µm (0.004") ID x 100' length PEEK tubing, red	Red 

Tubing | PEEK continued

WVR catalog number	Part description and detail	Color
SGEA1304005005-100F	360 µm OD x 125 µm (0.005") ID x 100' length PEEK tubing, green	Green ●
SGEA1304006002-100F	360 µm OD x 150 µm (0.006") ID x 100' length PEEK tubing, yellow	Yellow ●
SGEA1303062000-100F	1/8" OD x 0.062" ID x 100' length PEEK tubing, natural	Natural ●
SGEA1303080000-100F	1/8" OD x 0.080" ID x 100' length PEEK tubing, natural	Natural ●

PEEK tubing is available in custom colors, sizes and lengths upon request. Minimum order quantities will apply.

For more information about this product visit www.trajanscimed.com or contact techsupport@trajanscimed.com

Made in USA



AUSTRIA

VWR International GmbH
Graumannsgasse 7
1150 Wien
Tel.: +43 1 97 002 0
info.at@vwr.com

BELGIUM

VWR International bv
Researchpark Haasrode 2020
Geldenaaksebaan 464
3001 Leuven
Tel.: +32 (0) 16 385 011
vwr.be@vwr.com

CZECH REPUBLIC

VWR International s. r. o.
Veetee Business Park
Pražská 442
CZ - 281 67 Stříbrná Skalice
Tel.: +420 321 570 321
info.cz@vwr.com

DENMARK

VWR International A/S
Tobaksvejen 21
2860 Søborg
Tel.: +45 43 86 87 88
info.dk@vwr.com

FINLAND

VWR International Oy
Valimotie 9
00380 Helsinki
Tel.: +358 (0) 9 80 45 51
info.fi@vwr.com

FRANCE

VWR International S.A.S.
Le Périgares – Bâtiment B
201, rue Carnot
94126 Fontenay-sous-Bois cedex
Tel.: 0 825 02 30 30* (national)
Tel.: +33 (0) 1 45 14 85 00
(international)
info.fr@vwr.com
* 0,18 € TTC/min + prix appel

GERMANY

VWR International GmbH
Hilpertstraße 20a
D - 64295 Darmstadt
Tel.: 0800 702 00 07* (national)
Tel.: +49 (0) 6151 3972 0 (international)
info.de@vwr.com
*Freecall

HUNGARY

VWR International Kft.
Simon László u. 4.
4034 Debrecen
Tel.: +36 52 521130
info.hu@vwr.com

IRELAND

VWR International Ltd
Orion Business Campus
Northwest Business Park
Ballycoolin
Dublin 15
Tel.: +353 (0) 1 88 22 222
sales.ie@vwr.com

ITALY

VWR International S.r.l.
Via San Giusto 85
20153 Milano (MI)
Tel.: +39 02 3320311
info.it@vwr.com

THE NETHERLANDS

VWR International B.V.
Postbus 8198
1005 AD Amsterdam
Tel.: +31 (0) 20 4808 400
info.nl@vwr.com

NORWAY

VWR International AS
Brynsalleen 4,
0667 Oslo
Tel.: +47 22 90 00 00
info.no@vwr.com

POLAND

VWR International Sp. z o.o.
Limbowa 5
80-175 Gdansk
Tel.: +48 58 32 38 200
info.pl@vwr.com

PORTUGAL

VWR International - Material de
Laboratório, Lda
Centro Empresarial de Alfragide
Rua da Indústria, nº 6
2610-088 Amadora
Tel.: +351 21 3600 770
info.pt@vwr.com

SPAIN

VWR International Eurolab S.L.U.
C/ Tecnología 5-17
A-7 Llinars Park
08450 - Llinars del Vallès
Barcelona
Tel.: +34 902 222 897
info.es@vwr.com

SWEDEN

VWR International AB
Fagerstagatan 18a
163 94 Stockholm
Tel.: +46 (0) 8 621 34 00
kundservice.se@vwr.com

SWITZERLAND

VWR International GmbH
Lerzenstrasse 16/18
8953 Dietikon
Tel.: +41 (0) 44 745 13 13
info.ch@vwr.com

UK

VWR International Ltd
Customer Service Centre
Hunter Boulevard - Magna Park
Lutterworth
Leicestershire
LE17 4XN
Tel.: +44 (0) 800 22 33 44
uksales@vwr.com

CHINA

VWR (Shanghai) Co., Ltd
Bld.No.1, No.3728 Jinke Rd,
Pudong New District
Shanghai, 201203- China
Tel.: 400 821 8006
info_china@vwr.com

INDIA

Avantor Performance Materials India
Limited
17th Floor, Building No. 5, Tower C
DLF Cyber City Phase – III
Gurgaon - 122002, Haryana
Tel.: +91-1244-65-6700
help@avantoric.com

KOREA

VWR International ~
17, Daehak 4-ro, Yeongtong-gu,
Suwon-si, Gyeonggi-do
Tel.: +82 31 645 7256
saleskorea@avantorsciences.com

MIDDLE EAST & AFRICA

VWR International FZ-LLC
Office 203, DSP Lab Complex,
Dubai Science Park,
Dubai, United Arab Emirates
Tel: +971 4 5573271
Info.mea@vwr.com

SINGAPORE

VWR Singapore Pte Ltd
18 Gul Drive
Singapore 629468
Tel: +65 6505 0760
sales.sg@vwr.com

GO TO VWR.COM FOR THE LATEST NEWS, SPECIAL OFFERS AND DETAILS FROM YOUR LOCAL VWR SUPPORT TEAM