

## LC-MS Solutions

# Avantor® ACE® HPLC / UHPLC columns specification table

PHASE	USP LISTING	FUNCTIONAL GROUP	ENDCAPPED	PARTICLE SIZE (µm)	PORE SIZE (Å)	SURFACE AREA (m <sup>2</sup> /g)	CARBON LOAD (%)	pH RANGE	100% AQUEOUS COMPATIBLE
<b>Avantor® ACE® Traditional Chemistries</b>									
C18	L1	Octadecyl	Yes	1,7, 2, 3, 5, 10	100	300	15.5	2 – 8	-
C18-HL	L1	Octadecyl	Yes	3, 5, 10, 15	90	400	20	2 – 8	-
C8	L7	Octyl	Yes	2, 3, 5, 10	100	300	9	2 – 8	-
C4	L26	Butyl	Yes	2, 3, 5, 10	100	300	5.5	2 – 8	-
Phenyl	L11	Phenyl	Yes	2, 3, 5, 10	100	300	9.5	2 – 8	-
CN	L10	Cyano	Yes	2, 3, 5, 10	100	300	5.5	2 – 7	-
AQ	L1	Proprietary	Yes	2, 3, 5, 10	100	300	14	2 – 8	Yes
SIL	L3	Unbonded	No	2, 3, 5, 10	100	300	N/A	2 – 7	-
NH2	L8	Proprietary aminopropyl	Proprietary	1,7, 3, 5	100	300	3.5	2 – 7	Yes
<b>Avantor® ACE® Novel Chemistries</b>									
SuperC18	L1	Octadecyl encapsulated	Encapsulated	1,7, 2, 3, 5, 10	90	400	14.8	1.5 – 11.5	-
C18-AR	L1	Octadecyl with integral phenyl	Yes	1,7, 2, 3, 5, 10	100	300	15.5	2 – 8	Yes
C18-PFP	L1	Octadecyl with integral PFP	Yes	1,7, 2, 3, 5, 10	100	300	14.3	2 – 8	Yes
C18-Amide	L1 / L60	Polar embedded amide	Yes	1,7, 2, 3, 5, 10	100	300	16.4	2 – 8	Yes
CN-ES	L10	CN with extended alkyl spacer	Yes	1,7, 2, 3, 5, 10	100	300	12.6	2 – 8	Yes
<b>Solid Core Technology Avantor® ACE® Phases</b>									
UltraCore SuperC18	L1	Octadecyl encapsulated	Encapsulated	2.5	95	130	7	1.5 – 11.0	-
				5		100			
UltraCore SuperPhenylHexyl	L11	Phenyl Hexyl encapsulated	Encapsulated	2.5	95	130	4.6	1.5 – 11.0	-
				5		100			
<b>Large Molecule Wide Pore Avantor® ACE® Phases</b>									
C18-300	L1	Octadecyl	Yes	3, 5, 10	300	100	9	2 – 8	Yes
C8-300	L7	Octyl	Yes	3, 5, 10	300	100	5	2 – 8	Yes
C4-300	L26	Butyl	Yes	3, 5, 10	300	100	2.6	2 – 8	Yes
CN-300	L10	Cyano	Yes	3, 5, 10	300	100	2.6	2 – 7	Yes
Phenyl-300	L11	Phenyl	Yes	3, 5, 10	300	100	5.3	2 – 8	Yes
<b>Avantor® ACE® HILIC Phases</b>									
HILIC-A	L3	Proprietary SIL	No	1,7, 3, 5	100	300	N/A	2 – 7	-
HILIC-B	L8	Proprietary aminopropyl	No	1,7, 3, 5	100	300	4	2 – 7	-
HILIC-N	pending	Proprietary polyhydroxy	No	1,7, 3, 5	100	300	7	2 – 7	-
<b>Avantor® ACE® Method Development Kits (MDKs)</b>									
Advanced MDK	3 column kit	Contains C18, C18-AR, C18-PFP columns	Yes	1,7, 2, 3, 5	Data for these categories are as above for the individual column chemistries				
Extended MDK	3 column kit	Contains SuperC18, C18-Amide, CN-ES columns	Yes	1,7, 2, 3, 5					
UltraCore MDK	2 column kit	Contains SuperC18, SuperPhenylHexyl columns	Yes	2.5, 5					
Bioanalytical MDK	3 column kit	Contains C18-300, C4-300, Phenyl-300 columns	Yes	3, 5					
HILIC MDK	3 column kit	Contains HILIC-A, HILIC-B, HILIC-N columns	No	1,7, 3, 5					

As our channel brand, VWR, part of Avantor, offers an integrated, seamless purchasing experience that is optimized for the way you do business so you can obtain what you need to move your processes forward. For more information or to buy our products, please visit your local VWR website.

#### AUSTRIA

VWR International GmbH  
Graumannsgasse 7  
1150 Vienna  
Tel.: +43 1 97 002 0  
info.at@vwr.com

#### BELGIUM

VWR International bv  
Researchpark Haasrode 2020  
Geldenaaksebaan 464  
3001 Leuven  
Tel.: +32 (0) 16 385 011  
vwr.be@vwr.com

#### CANADA

VWR International  
2360 Argentia Road  
Mississauga, Ontario L5N 5Z7  
Tel.: +1 800 932 5000  
Canada\_Orders@vwr.com

#### CHINA

VWR (Shanghai) Co., Ltd  
Bld.No.1, No.3728 Jinke Rd,  
Pudong New District  
Shanghai, 201203- China  
Tel.: 400 821 8006  
info\_china@vwr.com

#### CZECH REPUBLIC

VWR International s. r. o.  
Veetee Business Park  
Pražská 442  
CZ - 281 67 Stříbrná Skalice  
Tel.: +420 321 570 321  
info.cz@vwr.com

#### DENMARK

VWR International A/S  
Tobaksvejen 21  
2860 Søborg  
Tel.: +45 43 86 87 88  
info.dk@vwr.com

#### FINLAND

VWR International Oy  
Valimotie 9  
00380 Helsinki  
Tel.: +358 (0) 9 80 45 51  
info.fi@vwr.com

#### FRANCE

VWR International S.A.S.  
Le Périgares – Bâtiment B  
201, rue Carnot  
94126 Fontenay-sous-Bois cedex  
Tel.: 0 825 02 30 30\* (national)  
Tel.: +33 (0) 1 45 14 85 00 (international)  
info.fr@vwr.com  
\* 0,18 € TTC/min + prix appel

#### GERMANY

VWR International GmbH  
Hilpertstraße 20a  
D - 64295 Darmstadt  
Tel.: 0800 702 00 07\* (national)  
Tel.: +49 (0) 6151 3972 0 (international)  
info.de@vwr.com  
\*Freecall

#### HUNGARY

VWR International Kft.  
Simon László u. 4.  
4034 Debrecen  
Tel.: +36 52 521130  
info.hu@vwr.com

#### INDIA

Avantor Performance Materials India Limited  
17th Floor, Building No. 5, Tower C  
DLF Cyber City Phase - III  
Gurgaon - 122002, Haryana  
Tel.: +91-1244-65-6700  
chromatography.india@avantorsciences.com

#### IRELAND

VWR International Ltd  
Orion Business Campus  
Northwest Business Park  
Ballycoolin  
Dublin 15  
Tel.: +353 (0) 1 88 22 222  
sales.ie@vwr.com

#### ITALY

VWR International S.r.l.  
Via San Giusto 85  
20153 Milano (MI)  
Tel.: +39 02 3320311  
info.it@vwr.com

#### KOREA

VWR International ~  
17, Daehak 4-ro, Yeongtong-gu,  
Suwon-si, Gyeonggi-do  
Tel.: +82 31 645 7256  
saleskorea@avantorsciences.com

#### THE NETHERLANDS

VWR International B.V.  
Postbus 8198  
1005 AD Amsterdam  
Tel.: +31 (0) 20 4808 400  
info.nl@vwr.com

#### MEXICO

VWR International, S.de R.L. de C.V.  
Km. 14.5 Carretera  
Tlalnepantla-Cuautitlán  
Col. Lechería  
Tultitlán Edo. de México  
CP 54940  
Tel.: +52 (55) 5005 0100  
vwrmx@vwr.com

#### MIDDLE EAST & AFRICA

VWR International FZ-LLC  
Office 203, DSP Lab Complex,  
Dubai Science Park,  
Dubai, United Arab Emirates  
Tel: +971 4 5573271  
Info.mea@vwr.com

#### NORWAY

VWR International AS  
Brynsalleen 4,  
0667 Oslo  
Tel.: +47 22 90 00 00  
info.no@vwr.com

#### POLAND

VWR International Sp. z o.o.  
Limbowa 5  
80-175 Gdansk  
Tel.: +48 58 32 38 200  
info.pl@vwr.com

#### PORTUGAL

VWR International -  
Material de Laboratório, Lda  
Centro Empresarial de Alfragide  
Rua da Indústria, nº 6  
2610-088 Amadora  
Tel.: +351 21 3600 770  
info.pt@vwr.com

#### SINGAPORE

VWR Singapore Pte Ltd  
18 Gul Drive  
Singapore 629468  
Tel: +65 6505 0760  
sales.sg@vwr.com

#### SPAIN

VWR International Eurolab S.L.U.  
C/ Tecnología 5-17  
A-7 Llinars Park  
08450 - Llinars del Vallès  
Barcelona  
Tel.: +34 902 222 897  
info.es@vwr.com

#### SWEDEN

VWR International AB  
Fagerstagatan 18a  
163 94 Stockholm  
Tel.: +46 (0) 8 621 34 00  
kundservice.se@vwr.com

#### SWITZERLAND

VWR International GmbH  
Lerzenstrasse 16/18  
8953 Dietikon  
Tel.: +41 (0) 44 745 13 13  
info.ch@vwr.com

#### UK

VWR International Ltd  
Customer Service Centre  
Hunter Boulevard - Magna Park  
Lutterworth  
Leicestershire  
LE17 4XN  
Tel.: +44 (0) 800 22 33 44  
uksales@vwr.com

#### UNITED STATES

VWR International, LLC  
100 Matsonford Road  
Building One Suite 200  
Radnor, PA 19087  
Tel.: +1 800 932 5000  
VWRCustomerService@vwr.com

### GO TO [VWR.COM](https://www.vwr.com) FOR THE LATEST NEWS, SPECIAL OFFERS AND DETAILS FROM YOUR LOCAL VWR SUPPORT TEAM

Prices, product, and/or services details are current when published and subject to change without notice. | Certain products or services may be limited by country, federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or affiliates. Offers valid in countries listed above, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its affiliates, unless otherwise noted. | Visit [vwr.com](https://www.vwr.com) to view our privacy policy, trademark owners, and additional disclaimers.